

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/17/16	

D

D

C




C

B

B

A

A

**SPECIFICATIONS:**

Material:

Insulator: Nylon66, rated UL 94V-0

Insulator color: Beige

Electrical:

Voltage rating: 250 VAC/DC

Current rating: 1A AC/DC

Contact resistance: 10 mohms max

Insulation resistance: 1,000Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 2 thru 10, 11, 12, 14, 15, 20, 25, 30

A =.049 [1.25] X No. of Spaces

B =.049 [1.25] X No. of Spaces + .071 [1.80]

C =.049 [1.25] X No. of Spaces + .114 [2.90]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
APPROVALS DRAWN HR 3/17/16 CHECKED SC 3/17/16 APPROVED							

6

5

4

3

2

1