




APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		UPDATE DRAWING	10/25/17	AY/NC



SECTION A-A



SECTION B-B



SECTION C-C

SPECIFICATIONS:

Material: Phosphor Bronze 0.15mm Thickness

Plating: Tin Plated

Electrical:

Current rating: 1 Amp max AC/DC

Contact resistance: 20 mohms max.

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 125 VAC for 1 minute

Mechanical:

Wire Range: 28-32 AWG.

Packaging: 15,000 Pcs / Reel

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X $\pm .10$ ϕ .X $\pm .10$
.XX $\pm .020$ ϕ .XX $\pm .015$
.XXX $\pm .015$ ϕ .XXX $\pm .010$

APPROVALS		DATE
DRAWN	BW	01/17/07
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE		1.25mm TERMINAL	
SIZE	PART NO.	REV.	
X	125CTB-R	A	
REF:	S00124T	SCALE:	NTS
SHEET 1 OF 1			