





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/5/07	
A		UPDATED DRAWING	12/18/17	HR/IC



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Phosphor Bronze, Tin plated

Solder Tabs: Brass, Tin plated

Electrical:

Voltage rating: 100V AC,DC

Current rating: 1A AC,DC

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

Positions: 02 thru 15

A = .049 [1.25] X No. of Spaces

B = .049 [1.25] X No. of Spaces + .114 [2.90]

C = .049 [1.25] X No. of Spaces + .197 [5.00]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	11/5/07
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.049 [1.25] PITCH WIRE TO BOARD HEADER
RIGHT ANGLE, SMT TYPE

SIZE	PART NO.	REV.
X	125SH-C-XX-TR-SMT-T/R	A
REF:	S00123T	SCALE: NTS SHEET 1 OF 1