





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	11227	RELEASED	4/11/11	
A		REVISED SHAPE & SPEC.	4/10/12	
B		UPDATE DRAWING	11/8/17	AY/TY



PACKAGED ON TAPE & REEL

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Phosphor Bronze, Tin plated

Solder Tabs: Brass, Tin plated

Electrical:

Voltage rating: 100V AC,DC

Current rating: 1A AC,DC

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Withstanding voltage: 500 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 15

A = .049 [1.25] X No. of Spaces

B = .049 [1.25] X No. of Spaces + .114 [2.90]

C = .049 [1.25] X No. of Spaces + .197 [5.00]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	DY	4/11/11
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE .049 [1.25] PITCH WIRE TO BOARD HEADER
STRAIGHT, SMT TYPE

SIZE	PART NO.	REV.
X	125SH-C-XX-TS-SMT-T/R	B
REF: S00123T		SCALE: NTS
		SHEET 1 OF 1