

6

5

4

3



2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		REVISED SPEC	9/8/11	



SPECIFICATIONS:

Material: Insulator: Hi-Temp. Thermoplastic, rated UL 94V-0

Insulator color: Natural

Plating: Tin over Copper underplate overall

Electrical: Operating voltage: 50 VAC max

Current rating: 1 Amp max

Contact resistance: 20 mohms max.

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating: Operating temperature: -25°C to +85°C

Environmental: Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		INCHES Holes .X ± .10 .XX ± .020 .XXX ± .015		Holes ØX ± .10 ØXX ± .015 ØXXX ± .010	
APPROVALS		DATE		TITLE	
DRAWN		BW		01/17/07	
CHECKED				SIZE	
APPROVED				PART NO.	
				1SH-A-XX-TR-SMT	
REF: S00016T		SCALE: NTS		SHEET 1 OF 1	

ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

1.0mm WIRE TO BOARD WAFER SMT

SIDE ENTRY