

6

5

4

3



2

1



Rev	AWO #	Description	Date	Appr
-		RELEASED	1/22/15	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 1 Amp max

Contact resistance: 20 mohms max

Insulation resistance: 5000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.

Positions: 6, 8, 10, 12, 14, 16, 18, 20, 22, 24, 26, 28, 30, 32, 34, 36
40, 44, 50, 60, 64 & 68
A = .079 [2.00] x No. of Spaces + .362 [9.20]
B = .079 [2.00] x No. of Spaces

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

2.0mm DUAL ROW, HORIZONTAL

MOUNT BOX HEADER, GOLD PLATED

SIZE

2BHR-XX-HUA-HT

REV.

-

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010
APPROVALS	
DRAWN	DATE
AY	1/22/15
CHECKED	DATE
GC	1/22/15
APPROVED	DATE

REF:	SCALE:	SHEET	1 OF 1
S00039T	NTS	1	1