





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/14/09	
A		REVISED DIM.	10/25/13	AY/NP



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating: Gold flash over Nickel underplate overall
Electrical: Current rating: 1 Amp max
Contact resistance: 20 mohms max
Insulation resistance: 5,000 Mohms min @ 500 VDC
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant



Positions: 2 thru 40
A = .079 [2.00] x No. of Positions
B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES Holes		TITLE .079 [2.00] SINGLE ROW PIN HEADER SURFACE MOUNT, TYPE A	
.X ± .10 .XX ± .020 .XXX ± .015 .XXX ± .015	ØXX ± .10 ØXXX ± .015 ØXXX ± .010	DATE	DATE
DRAWN	DY	7/14/09	
CHECKED			
APPROVED			
SIZE	PART NO.	REV.	
X	2PH1-XX-UA-SMT-A	A	
REF:	S00039T	SCALE:	NTS
		SHEET	1 OF 1

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710