

6

5

4

3

2


1

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/27/05	



APPROVED: _____

DATE: _____ TITLE: _____

D



C



B

B

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 1 Amp max.

Contact resistance: 20 mohms max. initial

Insulation resistance: 5,000 Mohms min.

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant

A

A

Positions: 04 thru 80
A = .079 [2.00] x No. of Positions per Row
B = .079 [2.00] x No. of Spaces

ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE .079 x .079 DUAL ROW RECEPTACLE STRIP

.110 [2.80] HEIGHT, RIGHT ANGLE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØXX	± .10	.X	± .10	ØXX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	SS		5/27/05				
CHECKED							
APPROVED							
				TITLE			
				.079 x .079 DUAL ROW RECEPTACLE STRIP			
				.110 [2.80] HEIGHT, RIGHT ANGLE			
				PART NO.			
				2RS2R-XX-G			
				REV.			
				-			
				SCALE: NTS			
				SHEET 1 OF 1			

6

5

4

3

2

1