





Rev	AWO #	Description	Date	Appr
-	-	RELEASED	12/15/06	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED
PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 100 VAC max

Current rating: 2 Amps max

Contact resistance: 10 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant

Positions: 2 thru 15
A = .079 [2.00] x No. of Positions + .153 [3.90]
B = .079 [2.00] x No. of Spaces
C = .079 [2.00] x No. of Positions + .024 [0.60]

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.079 [2.00] SHROUDED HEADER
RIGHT ANGLE, SURFACE MOUNT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØXX	± .10	.X	± .10	ØXX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	BW	12/15/06		TITLE			
CHECKED				.079 [2.00] SHROUDED HEADER			
APPROVED				RIGHT ANGLE, SURFACE MOUNT			
REF:				SCALE: NTS			
X				SHEET 1 OF 1			
SIZE				REV.			
PART NO.				-			
2SH-C-XX-TR-SMT							
909 Rahway Avenue, Union, NJ 07083							
Phone: 908-687-5000 Fax: 908-687-5710							
ADAM TECH							