





APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/7/08	
A		REVISED DIMENSION	8/30/11	
B		REVISED DIM.	02/04/13	



SPECIFICATIONS:

Material: Nylon 66, glass filled, rated UL 94V-0  
Contacts: Brass  
Plating: Tin over Copper underplate overall  
Electrical:  
Operating voltage: 250 VAC max  
Current rating: 3 Amps max  
Contact resistance: 10 mohms max  
Insulation resistance: 1,000 Mohms min @ 500 VDC  
Dielectric withstanding voltage: 800 VAC for 1 minute  
Temperature Rating:  
Operating temperature: -25°C to +85°C  
Environmental:  
Lead free, RoHS compliant

Positions: 6 thru 32  
A = .079 [2.00] x No. of Spaces  
B = .079 [2.00] x No. of Positions per Row + .029 [0.74]  
C = .079 [2.00] x No. of Positions per Row + .029 [0.74]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØXX	± .10	.X	± .10	ØXX	± .10
.XX	± .020	ØXXX	± .015	.XX	± .015	ØXXX	± .010
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	SS	5/7/08		TITLE	.079 [2.00] DOUBLE ROW, SHROUDED HEADER, STRAIGHT, PCB		
CHECKED				SIZE	PART NO.	2SHD-C-XX-TS	REV. B
APPROVED				REF:	SCALE: NTS	SHEET 1 OF 1	

**ADAM TECH**

909 Railway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710