



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/27/18	



SPECIFICATIONS:

Material:
 Insulator: PA6T, rated UL 94V-0
 Insulator color: Black
 Contacts: CuZn30 H140
 Plating:
 Matte Tin over Nickel underplate overall
 Electrical:
 Contact resistance: 20 mohms max
 Insulation resistance: 10G ohms min
 Dielectric withstanding voltage: 1000V/60S
 Temperature Rating:
 Operating temperature: -40°C to +125°C
 Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED MM ± 0.30 X.XX ± 0.25 X.XXX ± 0.10 ANGLE ± 3°		ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		DATE	
DRAWN	AY	11/27/18	
CHECKED	AC	11/27/18	
APPROVED			
TITLE		2.54 PITCH PIN HEADER, 1*4 PIN, STRAIGHT	
SIZE	PART NO.	REV.	
X	ADT-AMP1251104S2BS192A1	-	
REF:	S00111C	SCALE:	NTS
SHEET 1 OF 1			