




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/27/18	



SPECIFICATIONS:

Material:
 Insulator: PA6T+30%GF, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass
 Plating:
 Matte Tin over Nickel underplate overall
 Electrical:
 Current rating: 3 Amp
 Contact resistance: 20 mohms max
 Insulation resistance: 1,000 Mohms min
 Dielectric withstanding voltage: 500 VAC
 Temperature Rating:
 -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED MM ANGLE X.X ± 0.25 ± 3° X.XX ± 0.20 X.XXX ± 0.10		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		DATE	
DRAWN	AY	11/27/18	
CHECKED	AC	11/27/18	
APPROVED			
TITLE		2.54 PITCH PIN HEADER, 1*6 PIN, STRAIGHT	
SIZE	PART NO.	REV.	
X	ADT-AMP1251106S4BS165A1	-	
REF:	S00111C	SCALE:	NTS
SHEET 1 OF 1			