




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/25/20	



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:
 Housing: Hi-temp thermoplastic, Color: Black
 Contact: Phosphor Bronze, Gold plated
 Electrical:
 Contact resistance: 30 mohms max
 Insulation resistance: 1,000 Megaohms ohms min
 Dielectric Voltage: 500 VAC one sec level
 Temperature Rating:
 Operating temperature: -25°C to +85°C
 Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE MILLIMETERS
 TOLERANCES: EXCEPT AS NOTED
 MM ANGLE
 X ± 0.30 X ± 1°
 X.X ± 0.25 X.X ± 0.5°
 X.XX ± 0.20
 X.XXX ± 0.10

ADAM
TECH
 INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLES			
BATTERY HOLDER, FOR TWO "AAA" CELLS, SMT			
SIZE	PART NO.	REV.	
X	BH-102B-5	-	
REF: S00136C	SCALE: NTS	SHEET 1 OF 1	

APPROVALS		DATE
DRAWN	LH	3/25/20
CHECKED	MY	3/25/20
APPROVED		