



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/24/18	



SPECIFICATIONS:

Material:

Housing: PA66, Color: Black

Contact: Stainless Steel, Nickel plated

Electrical:

Contact resistance: 30 Milliohms max

Insulation resistance: 1,000 Mega ohms min

Dielectric Voltage: 500 VAC one sec level

Temperature Rating:

Operating temperature: -55°C to +105°C.

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 ØX ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010		ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		TITLE	
DATE		COIN CELL BATTERY HOLDER FOR ONE CELL CR2032	
DRAWN	AY	10/24/18	
CHECKED	RC1	10/24/18	
APPROVED			
SIZE		PART NO.	
X		BH-50C-1	
REF:		S00136C	
SCALE:		NTS	
SHEET		1 OF 1	