

6

5

4

3


2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/12/20	



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:

Housing: PA66, rated UL94V-0, Color: Black

Contact: Brass, Nickel plated

Electrical:

Contact resistance: 30 Milliohms max

Insulation resistance: 1,000 Megohms ohms min

Dielectric Voltage: 500 VAC @ sea level

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED
MM ANGLE

X	± 0.30	X	± 1°
X.X	± 0.25	X.X	± 0.5°
X.XX	± 0.20		
X.XXX	± 0.10		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

APPROVALS		DATE
DRAWN	LH	3/12/20
CHECKED	MY	3/12/20
APPROVED		

TITLE BATTERY HOLDER, PCB THRU HOLE
FOR 2032, DIP TYPE

SIZE X	PART NO. BH-80B-1	REV. -
REF: S00136C	SCALE: NTS	SHEET 1 OF 1