





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/10/05	
A		RELEASED	10/27/10	



RECOMMENDED PCB LAYOUT



SPECIFICATION:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator Color: Black

Metal Latch: Zinc Alloy, Nickel plated.

Contacts: Brass

Contact Plating:

Gold Flash over Nickel underplate overall

Electrical:

Operating Voltage: 350V AC max.

Current rating: 3 Amps max.

Contact resistance: 20 mohms max

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 1000 VAC / minute

Temperature Rating:

Operating temperature: -40°C TO +105°C

Environmental:

Lead free, RoHS compliant.

Recommended soldering temp: 235°C for 5 sec.

Positions: 06, 08, 10, 14, 16, 20, 26, 30, 34, 40, 50, 60, 64
A = .100 [2.54] X No. of Positions / 2 + .300 [7.62]
B = .100 [2.54] X No. of Positions / 2 + .088 [2.24]
C = .100 [2.54] X No. of Positions / 2 - .100 [2.54]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

BOX HEADER, HORIZONTAL PCB MOUNT,
2 ROW .100 PITCH, GOLD PLATED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				ADAM TECH			
.X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010				909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
APPROVALS		DATE		TITLE BOX HEADER, HORIZONTAL PCB MOUNT, 2 ROW .100 PITCH, GOLD PLATED			
DRAWN	SS	5/10/05					
CHECKED							
APPROVED							
SIZE		PART NO.					
X		BHR-XX-HUA-ML		REV. A			
REF: S00019C		SCALE: NTS		SHEET 1 OF 1			