


Rev	AWO #	Description	Date	Appr
-		RELEASED	1/26/05	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Soft PVC

Snap terminals: Brass, Nickel plated

Wire: 26 AWG, PVC insulation

Electrical:

Operating voltage: 9 VDC max.

Temperature Rating:

Operating temperature: -10°C to +180°C

Environmental:

Lead free, RoHS compliant



ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

BATTERY SNAP, STANDARD LENGTH LEADS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
APPROVALS		DATE		TITLE BATTERY SNAP, STANDARD LENGTH LEADS			
DRAWN	SS	1/26/05					
CHECKED							
APPROVED							
SIZE		PART NO.		REF: SCALE: NTS SHEET 1 OF 1			
X		BS-1-1		REV: -			