


APPROVED: _____
 DATE: _____ TITLE: _____
 CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/13/15	
A		ADDED 1FT PART NUMBER	5/3/19	AY/TW



PIN ASSIGNMENT			
P1			P2
1 — RED		1 — WHITE	
2 — WHITE		2 — WHITE	
3 — GREEN		3 — GREEN	
4 — BLACK		4 — GREEN	
SHELL — BRAID		SHELL	

ADAM P/N	L
CA-USB-AM/AF-1FT	12.008"±.787" [305±20mm]
CA-USB-AM/AF-3FT	36.024"±1.181" [915±30mm]
CA-USB-AM/AF-6FT	72.047"±1.969" [1830±50mm]
CA-USB-AM/AF-10FT	120.079"±1.969" [3050±50mm]

SPECIFICATIONS:
Connector:
 P1= USB Connector 2.0 A Type Plug, Insulator Color: White, Overmold Color: Black, 50P PVC
 P2= USB Connector 2.0 A Type Socket, Insulator Color: White, Overmold Color: Black, 50P PVC
Cable:
 UL2725, (1P+2C)+A+B, OD: .189" [4.8mm] (28/24),Jacket Color: Black .
Electrical Test:
 All Assemblies must be 100% Tested for
 Shorts, Open, Continuity, and Physical Appearance.
Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			
INCHES		HOLES	
.X ± .10	Ø.X ± .10		
.XX ± .020	Ø.XX ± .015		
.XXX ± .015	Ø.XXX ± .010		
APPROVALS		DATE	
DRAWN	HR	10/13/15	
CHECKED	TW	10/13/15	
APPROVED			

ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
TITLE CUSTOMER ASSEMBLY, USB 2.0 PLUG TYPE A TO USB 2.0 SOCKET TYPE A			
SIZE X	PART NO. CA-USB-AM/AF-XFT	REV. A	
REF: S00087T	SCALE: NTS	SHEET 1 OF 1	