

6

5

4

3

2


1

APPROVED: _____

DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/13/15	



PIN ASSIGNMENT			
P1		P2	
1	RED	1	
2	WHITE	2	
3	GREEN	3	
4	BLACK	4	
5	BLUE	5	
6	YELLOW	6	
7		7	
8	PURPLE	8	
9	ORANGE	9	
S	BRAID	S	

ADAM P/N	L
CA-USB3-AM/AF-3FT	36.024"±1.181" [915±30mm]
CA-USB3-AM/AF-6FT	72.047"±1.969" [1830±50mm]
CA-USB3-AM/AF-10FT	120.079"±1.969" [3050±50mm]

SPECIFICATIONS:**Connector:**P1= USB 3.0 Connector A type Plug, Gold Flash Plated,
Insulator Color: Blue, Overmold Color: Blue, 50P PVCP2= USB 3.0 Connector A type Socket, Gold Flash Plated,
Insulator Color: Blue, Overmold Color: Blue, 50P PVC**Cable:**UL20276, (30#*1P+D+A+M)*2C+30#*1P+26#*2C+A+B,
OD: .189" [4.8mm], Jacket Color Blue.**Electrical Test:**All Assemblies must be 100% Tested for
Shorts, Open, Continuity, and Physical Appearance.**Environmental:**

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
.X ± .10	Ø.X ± .10	TITLE		CUSTOM ASSEMBLY, USB 3.0 PLUG TYPE A USB 3.0 SOCKET TYPE A			
.XX ± .020	Ø.XX ± .015	APPROVALS		SIZE	PART NO.	REV.	
.XXX ± .015	Ø.XXX ± .010	DRAWN	HR	X	CA-USB3-AM/AF-XFT	-	
DATE		CHECKED	TW	REF:	S00087T	SCALE:	NTS
10/13/15		APPROVED		SHEET 1 OF 1			