


6		5		4		3		2		1																																																																					
APPROVED: _____						Rev	AWO #	Description	Date	Appr																																																																					
DATE: _____ TITLE: _____						-		RELEASED	10/13/15																																																																						
CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE																																																																															
																																																																															
<table border="1"><caption>PIN ASSIGNMENT</caption><thead><tr><th>P1</th><th></th><th>P2</th></tr></thead><tbody><tr><td>1</td><td>RED</td><td>1</td></tr><tr><td>2</td><td>WHITE</td><td>2</td></tr><tr><td>3</td><td>GREEN</td><td>3</td></tr><tr><td>4</td><td>BLACK</td><td>4</td></tr><tr><td>5</td><td>BLUE</td><td>5</td></tr><tr><td>6</td><td>YELLOW</td><td>6</td></tr><tr><td>7</td><td></td><td>7</td></tr><tr><td>8</td><td>PURPLE</td><td>8</td></tr><tr><td>9</td><td>ORANGE</td><td>9</td></tr><tr><td>S</td><td>BRAID</td><td>S</td></tr></tbody></table>												P1		P2	1	RED	1	2	WHITE	2	3	GREEN	3	4	BLACK	4	5	BLUE	5	6	YELLOW	6	7		7	8	PURPLE	8	9	ORANGE	9	S	BRAID	S																																			
P1		P2																																																																													
1	RED	1																																																																													
2	WHITE	2																																																																													
3	GREEN	3																																																																													
4	BLACK	4																																																																													
5	BLUE	5																																																																													
6	YELLOW	6																																																																													
7		7																																																																													
8	PURPLE	8																																																																													
9	ORANGE	9																																																																													
S	BRAID	S																																																																													
<table border="1"><thead><tr><th>ADAM P/N</th><th>L</th></tr></thead><tbody><tr><td>CA-USB3-AM/BM-3FT</td><td>36.024"±1.181" [915±30mm]</td></tr><tr><td>CA-USB3-AM/BM-6FT</td><td>72.047"±1.969" [1830±50mm]</td></tr><tr><td>CA-USB3-AM/BM-10FT</td><td>120.079"±1.969" [3050±50mm]</td></tr></tbody></table>												ADAM P/N	L	CA-USB3-AM/BM-3FT	36.024"±1.181" [915±30mm]	CA-USB3-AM/BM-6FT	72.047"±1.969" [1830±50mm]	CA-USB3-AM/BM-10FT	120.079"±1.969" [3050±50mm]																																																												
ADAM P/N	L																																																																														
CA-USB3-AM/BM-3FT	36.024"±1.181" [915±30mm]																																																																														
CA-USB3-AM/BM-6FT	72.047"±1.969" [1830±50mm]																																																																														
CA-USB3-AM/BM-10FT	120.079"±1.969" [3050±50mm]																																																																														
<table border="1"><tr><td colspan="4">SPECIFICATIONS:</td></tr><tr><td colspan="4">Connector:</td></tr><tr><td colspan="4">P1= USB 3.0 Connector A type Plug, Gold Flash Plated, Insulator Color: Blue, Overmold Color: Blue, 50P PVC</td></tr><tr><td colspan="4">P2= USB 3.0 Connector B type Plug, Gold Flash Plated, Insulator Color: Blue, Overmold Color: Blue, 50P PVC</td></tr><tr><td colspan="4">Cable:</td></tr><tr><td colspan="4">UL20276, (30#*1P+D+A+M)*2C+30#*1P+26#*2C+A+B, OD: .189" [4.8mm], Jacket Color Blue</td></tr><tr><td colspan="4">Electrical Test:</td></tr><tr><td colspan="4">All Assemblies must be 100% Tested for Shorts, Open, Continuity, and Physical Appearance.</td></tr><tr><td colspan="4">Environmental:</td></tr><tr><td colspan="4">Lead free, RoHS compliant</td></tr></table>												SPECIFICATIONS:				Connector:				P1= USB 3.0 Connector A type Plug, Gold Flash Plated, Insulator Color: Blue, Overmold Color: Blue, 50P PVC				P2= USB 3.0 Connector B type Plug, Gold Flash Plated, Insulator Color: Blue, Overmold Color: Blue, 50P PVC				Cable:				UL20276, (30#*1P+D+A+M)*2C+30#*1P+26#*2C+A+B, OD: .189" [4.8mm], Jacket Color Blue				Electrical Test:				All Assemblies must be 100% Tested for Shorts, Open, Continuity, and Physical Appearance.				Environmental:				Lead free, RoHS compliant																															
SPECIFICATIONS:																																																																															
Connector:																																																																															
P1= USB 3.0 Connector A type Plug, Gold Flash Plated, Insulator Color: Blue, Overmold Color: Blue, 50P PVC																																																																															
P2= USB 3.0 Connector B type Plug, Gold Flash Plated, Insulator Color: Blue, Overmold Color: Blue, 50P PVC																																																																															
Cable:																																																																															
UL20276, (30#*1P+D+A+M)*2C+30#*1P+26#*2C+A+B, OD: .189" [4.8mm], Jacket Color Blue																																																																															
Electrical Test:																																																																															
All Assemblies must be 100% Tested for Shorts, Open, Continuity, and Physical Appearance.																																																																															
Environmental:																																																																															
Lead free, RoHS compliant																																																																															
<table border="1"><tr><td colspan="4">UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED</td><td colspan="4">ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710</td></tr><tr><td colspan="4">INCHES</td><td colspan="4">HOLES</td></tr><tr><td>.X</td><td>± .10</td><td>Ø.X</td><td>±.10</td><td colspan="4" rowspan="3">TITLE CUSTOM ASSEMBLY, USB 3.0 PLUG TYPE A USB 3.0 PLUG TYPE B</td></tr><tr><td>.XX</td><td>± .020</td><td>Ø.XX</td><td>±.015</td></tr><tr><td>.XXX</td><td>± .015</td><td>Ø.XXX</td><td>±.010</td></tr><tr><td colspan="4">APPROVALS</td><td colspan="4">DATE</td></tr><tr><td colspan="2">DRAWN</td><td colspan="2">HR</td><td colspan="2">10/13/15</td><td colspan="2" rowspan="3">SIZE X</td></tr><tr><td colspan="2">CHECKED</td><td colspan="2">TW</td><td colspan="2">10/13/15</td></tr><tr><td colspan="2">APPROVED</td><td colspan="2"></td><td colspan="2"></td></tr><tr><td colspan="4">REF: S00087T</td><td colspan="2">SCALE: NTS</td><td colspan="2">SHEET 1 OF 1</td></tr></table>												UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710				INCHES				HOLES				.X	± .10	Ø.X	±.10	TITLE CUSTOM ASSEMBLY, USB 3.0 PLUG TYPE A USB 3.0 PLUG TYPE B				.XX	± .020	Ø.XX	±.015	.XXX	± .015	Ø.XXX	±.010	APPROVALS				DATE				DRAWN		HR		10/13/15		SIZE X		CHECKED		TW		10/13/15		APPROVED						REF: S00087T				SCALE: NTS		SHEET 1 OF 1	
UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710																																																																											
INCHES				HOLES																																																																											
.X	± .10	Ø.X	±.10	TITLE CUSTOM ASSEMBLY, USB 3.0 PLUG TYPE A USB 3.0 PLUG TYPE B																																																																											
.XX	± .020	Ø.XX	±.015																																																																												
.XXX	± .015	Ø.XXX	±.010																																																																												
APPROVALS				DATE																																																																											
DRAWN		HR		10/13/15		SIZE X																																																																									
CHECKED		TW		10/13/15																																																																											
APPROVED																																																																															
REF: S00087T				SCALE: NTS		SHEET 1 OF 1																																																																									
<table border="1"><tr><td colspan="2">PART NO.</td><td colspan="2">CA-USB3-AM/BM-XFT</td><td colspan="2">REV.</td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2">-</td></tr></table>												PART NO.		CA-USB3-AM/BM-XFT		REV.						-																																																									
PART NO.		CA-USB3-AM/BM-XFT		REV.																																																																											
				-																																																																											

