

APPROVED: _____



DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE/NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/13/15	
A		UPDATE DRAWING	1/2/18	AY/RC1
B		UPDATE DRAWING	6/10/19	AY/LW
C		UPDATE SPEC.	7/12/19	AY/TW
D		UPDATE DRAWING	11/11/19	AY/RC
E		ADDED 3.5FT LONG P/N	1/9/20	AY/INP
F		ADDED 6 FT LONG P/N	4/10/20	SS
G		ADDED 4FT & 5FT P/N	9/15/20	AY/YC

P1

P2



PIN ASSIGNMENT

P1	P2	COLOR
1	1	VBUS RED
2	2	D- WHITE A7
3	3	D+ GREEN A6
4	4	GND BLACK
Shell	Shell	Braid

ADAM P/N	L
CA-USB-AM/CM-1FT	12.008" ± .394" [305 ± 10mm]
CA-USB-AM/CM-3FT	36.024" ± .787" [915 ± 20mm]
CA-USB-AM/CM-3.5FT	42.000" ± 1.181" [1066.8 ± 30mm]
CA-USB-AM/CM-4FT	47.244" ± 1.181" [1200 ± 30mm]
CA-USB-AM/CM-5FT	59.055" ± 1.181" [1500 ± 30mm]
CA-USB-AM/CM-6FT	72.000" ± 2.36" [1830 ± 60mm]

TEST CONDITION:

1. 100% OPEN SHORT & MISWIRE TEST.
2. CONDUCTOR RESISTANCE: 3 Ohms Max.
3. INSULATION RESISTANCE: 5M Ohms Min.

SPECIFICATIONS:

Connectors:

P1= USB Connector A type Plug, Insulator color: White, Overmold Color: Black, PVC

P2= USB Connector C type Plug, (Crimping Shell) Overmold Color: Black, PVC, W/ PCB, <REV:2.0>

Wire:

UL2725 28AWG*1P+24AWG*2C+AEB, OD: .165" [4.2mm], Jacket Color Black, PVC

Electrical:

Rating: 5V/2A

Dielectric withstanding voltage: 300 VDC

Electrical Test:

All assemblies must be 100% tested for shorts, open continuity and physical appearance.

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	HR	10/13/15
CHECKED	TW	10/13/15
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
CUSTOMER ASSEMBLY, USB 2.0 PLUG TYPE A
TO USB 3.1 PLUG TYPE C

SIZE	PART NO.	REV.
X	CA-USB-AM/CM-XFT	G
REF:	S00161C	SHEET 1 OF 1