APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/1/22	
A		UPDATE SPEC.	11/30/22	WX/RC

Ⓐ Lock Nut



Ⓑ Washer





Ⓒ Body



Ⓓ Seal



Ⓔ Sealing Nut





RECOMMENDED
PANEL CUT–OUT
(.094 [2.4] MAX PANEL THICKNESS)

SPECIFICATIONS:

Material:

Look Nut: PA66, rated UL 94V–2
Body: PA66, rated UL 94V–2
Sealing Nut: PA66, rated UL 94V–2
Washer: Nitrile Butylene
Seal: Nitrile Butylene

Mechanical:

Cable range O.D.: ø.236~ø.433 [6.00~11.00mm]
Nut Torque: 2Nm Max.

Environmental:

Waterproof: IP68
Lead free, RoHS compliant. RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	ØX	±.10
.XX	± .020	ØXX	±.015
.XXX	± .015	ØXXX	±.010

DRAWN	LH	11/1/22
CHECKED	RC	11/1/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: WATERPROOF CONNECTOR, PG13.5, 1 HOLE, CABLE GLAND, WATERPROOF: IP68

SIZE	PART NO.	REV.
X	CG-P-13.5	A

REF:	SCALE:	SHEET
S00211C	NTS	1 OF 1