









APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/1/22	
A		UPDATED SPEC.	11/30/22	JJ/RC



SPECIFICATIONS:

Material:
 Lock Nut: PA66, rated UL 94V-2
 Body: PA66, rated UL 94V-2
 Sealing Nut: PA66, rated UL 94V-2
 Claw: PA66, rated UL 94V-2
 Washer: NBR
 Seal: NBR
 Mechanical:
 Cable Range (O.D.): 56-66mm
 Thread O.D. L2: 75mm
 Thread Length L2: 25mm
 Spanner Size A&E: 92/92mm
 Nut Torque: 5Nm Max.
 Environmental:
 Waterproof: IP68
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

DRAWN	WX	11/1/22
CHECKED	RC	11/1/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

**ADAM
TECH**

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE: WATERPROOF CONNECTOR, M75, 1 HOLE,
 CABLE GLAND, WATERPROOF: IP68

SIZE X	PART NO. CG-P-M75-2.0	REV. A
REF: S00211C	SCALE: NTS	SHEET 1 OF 1