





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/11/05	
A		REVISED LOW FEET DIM.	3/20/08	
B		REDRAWN	6/30/14	HR/QZL



SPECIFICATIONS:

Material:

Contact: Phosphor Bronze

Plating:

Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 20 mohms max initial

Mechanical:

Recommended wire range: 24–28 AWG

Temperature Rating:

Operating temperature: –55°C to +105°C


Packaging:

B = Loose Cut

R = Tape and Reel

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES
.X ± .10
.XX ± .020
.XXX ± .015

HOLES
ØX ± .10
ØXX ± .015
ØXXX ± .010

APPROVALS

DATE

DRAWN SS 1/11/05

CHECKED

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

D-SUB PLUG CONTACT, 24-28 AWG

GOLD FLASH

TITLE

SIZE PART NO.

X

DCP-01-X

REF: S00087T

SCALE: NTS

SHEET 1 OF 1

REV. B