

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description



Date

Appr


-

RELEASED

12/2/19




SECTION A-A



SECTION B-B

Reel package direction: As below shown.



Direction

Crimping side upper
Strip carrier on top.

SPECIFICATIONS:

Material:

Terminal: 0.30MM Thickness, Brass, Tin plated

Mechanical:

Wire Range: #18~22 AWG

Insulator O.D: 2.80~2.40MM

Environmental:

Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED
ANGLE

MM	ANGLE
.X ± 0.35	X.* ± 2°
.XX ± 0.25	.X* ± 1°
.XXX ± 0.15	.XX* ± 0.5°

APPROVALS

DATE

DRAWN

OW

12/2/19

CHECKED

AC

12/2/19

APPROVED

ADAM
TECH
INTERCONNECTS909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

MALE CRIMP FOR DDH SERIES
TIN PLATED, ON REELS

SIZE

X

PART NO.

DMC-01D-R

REV.

-

REF:

S00119T

SCALE: NTS

SHEET 1 OF 1