







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/2/18	
A		UPDATE DRAWING	2/19/20	AY/AY1
B		UPDATE DRAWING	2/21/20	LH/AY1
C		UPDATE DIM.	11/12/20	LH/JL



RECOMMENDED PANEL CUT

Poles	Dimensions			
	A	B	C	D
02	.565 [14.35]	.532 [13.50]	.340 [8.64]	.095 [2.41]
03	.815 [20.70]			
04	1.065 [27.05]			
05	1.315 [33.40]			
06	1.567 [39.80]			
07	1.817 [46.15]			
08	2.067 [52.50]			
09	2.317 [58.85]			
10	2.567 [65.20]			

Poles	Dimensions					
	A		B		C	
02	.250	[6.35]	.550	[13.97]	1.079	[27.40]
03	.500	[12.70]	.800	[20.32]	1.079	[27.40]
04	.750	[19.05]	1.050	[26.67]	1.079	[27.40]
05	1.000	[25.40]	1.307	[33.20]	1.083	[27.50]
06	1.250	[31.75]	1.550	[39.37]	1.567	[39.80]
07	1.562	[38.10]	1.800	[45.72]	1.817	[46.15]
08	1.750	[44.45]	2.050	[52.07]	2.067	[52.50]
09	2.000	[50.80]	2.300	[58.42]	2.317	[58.85]
10	2.250	[57.15]	2.550	[64.77]	2.567	[65.20]

SPECIFICATIONS:

Material:

Insulator: Nylon66, rated UL 94V-2

Insulator color: Natural

Electrical:

Current rating: 02~10P: 12 Amp max (With UL1015, 12AWG)

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 2,900 VAC for 1 minute

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ±.10 Ø.X ±.10
.XX ±.020 Ø.XX ±.015
.XXX ±.015 Ø.XXX ±.010

APPROVALS		DATE
DRAWN	HR	3/2/18
CHECKED	AC	3/2/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE		.250 [6.35MM] PITCH CONNECTOR, HOUSINGS, FEMALE, VERTICAL		
SIZE	PART NO.	DME-F2-XX		REV. C
REF:	S00124T	SCALE:	NTS	SHEET 1 OF 1