



6 5 4 3 2 1



APPROVED: _____

DATE: _____ TITLE: _____



Rev	AWO #	Description	Date	Appr
-		RELEASED	2/21/20	





6 POSITION




9 POSITION




12 POSITION



15 POSITION



RECOMMENDED
PCB LAYOUT
(TRIPLE ROW)



ALL MALE PIN

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: Natural

Contacts: Phosphor Bronze, Tin plated

Electrical:

Current rating: 06~15P: 9 Amp Max (With UL1007, 16AWG)

Contact resistance: 20 mohms max

Insulation resistance: 1,000M ohms min

Dielectric withstanding voltage: 2,900 VAC for 1 minute

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant.



$A = .250 [6.35] \times \text{No. of Spaces}$

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710				
					TITLE WIRE TO BOARD, FEMALE, 6.35mm PITCH, WITH POLARIZING PEG, MALE PIN		
APPROVALS		DATE		SIZE X PART NO. DME-XX-S2-P-SQ REV. - -			
DRAWN	LH	2/21/20					
CHECKED	AY1	2/21/20					
APPROVED							
		REF: S00124T		SCALE: NTS		SHEET 1 OF 1	