






Rev	AWO #	Description	Date	Appr
-		RELEASED	11/19/10	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PANEL HOLE



SPECIFICATIONS:

Material:

Insulator: Thermoplastic, rated UL94V-2

Insulator color: Natural

Contact: Copper Alloy

Electrical:

Current rating: 13A

Voltage rating: 600V

Insulation resistance: 1,000 Mohms min.

Withstand voltage: 5000V AC/ minute

Temperature range: -55°C to +105°C

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

.250 [6.35] WIRE TO WIRE, FEMALE, 3 POLES

TITLE

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES

.X ± .10 ØXX ± .10

.XX ± .020 ØXXX ± .015

.XXX ± .015 ØXXX ± .010

APPROVALS

DATE

DRAWN DY 11/19/10

CHECKED

APPROVED

SIZE PART NO.

X

DME-F-03

REV.

-

REF: S00004T

SCALE: NTS

SHEET 1 OF 1