



Rev	AWO #	Description	Date	Appr
-		RELEASED	04/04/05	

APPROVED: _____

DATE: _____ TITLE: _____



DSR-XX	NO. OF CONTACTS	DIMENSION	
		A	B
DSR-09	9	.885 [22.48]	.630 [16.00]
DSR-15	15	1.212 [30.78]	.943 [23.95]
DSR-25	25	1.754 [44.55]	1.437 [36.50]
DSR-37	37	2.414 [61.32]	2.035 [51.64]

SPECIFICATIONS:

Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Environmental:
Lead free, RoHS compliant.

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
STRAIN RELIEF, DSR SERIES IDC D-SUBS
9, 15, 25 & 37 POSITION

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		HOLE	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010
APPROVALS		DATE	
DRAWN	SS	04/04/05	
CHECKED			
APPROVED			
SIZE	PART NO.	REV.	
X	DSR-XX	-	
REF:	SCALE: NTS	SHEET 1 OF 1	