



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/9/19	



SPECIFICATIONS:

Material:
 Insulator: Glass filled thermoplastic, rated UL 94V-0
 Insulator Color: Black
 Contacts: Brass
 Shell: Steel, Nickel plated
 Plating:
 Gold flash over Nickel underplate on mating area,
 Tin over Copper underplate on tailss
 Electrical:
 Rating: 1.5 Amp @ 40 VAC (rms)
 Contact resistance: 20 mohms max
 Insulation resistance: 1000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 500 VAC (rms)
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010		ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		DATE	
DRAWN	AY	4/9/19	
CHECKED	LW	4/9/19	
APPROVED			
TITLE		DVI CONNECTOR, 24+5PINS, MALE STRAIGHT, ANALOG	
SIZE	PART NO.	REV.	
X	DVI-PT-24-2-01	-	
REF:	S00223T	SCALE:	NTS
SHEET 1 OF 1			