





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/6/16	
A		UPDATE DRAWING	8/31/20	AY/KC



SPECIFICATIONS:

Material:
 Insulator: PA66, rated UL 94V-0
 Insulator color: Grey
 Contact: Copper Alloy, Tin plated
 Electrical:
 Voltage rating: 300V
 Current rating: 4A
 Dielectric withstanding voltage: 1600V for 1 minute
 Mechanical:
 Wire range: 28~20 AWG
 Strip length: 8.5~9.5 mm
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant.



Positions: 01 thru 30

A= .098 [2.50] x No. of Positions + .059 [1.50]

B= .098 [2.50] x No. of Space

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES		HOLES		INTERCONNECTS	
.X	± .10	Ø.X	± .10	TITLE	
.XX	± .020	Ø.XX	± .015	EURO BLOCK, .098 [2.50] PITCH, WITH END COVER	
.XXX	± .015	Ø.XXX	± .010	DOUBLE ROW CENTER CONTACT LINK	
APPROVALS		DATE		SIZE	PART NO.
DRAWN	AY	7/6/16		X	EB59A-XX-V
CHECKED	YC	7/6/16		REV.	A
APPROVED				REF:	S00067C
				SCALE:	NTS
				SHEET 1 OF 1	