





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/15	
A		UPDATE SPEC.	1/14/21	LH/LX



RECOMMENDED PCB LAYOUT



SECTION A-A

SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Contacts: Copper Alloy, Tin plated

Electrical:

Voltage rated: 300 V

Current rated: 15 A

Dielectric withstanding voltage: 1,600 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 24

A = .197 [5.00] x No. of Positions+ .055 [1.40]

B = .197 [5.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE MM [INCHES]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS DATE

DRAWN	HR	4/8/15
-------	----	--------

CHECKED	NC	4/8/15
---------	----	--------

APPROVED		
----------	--	--

ADAM
TECH

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE .197 [5.00] PITCH, EURO BLOCK HEADER
 RIGHT ANGLE, CLOSE SIDE

SIZE X	PART NO. EBQA-XX-C-C	REV. A
-----------	-------------------------	-----------

REF: S00067C	SCALE: NTS	SHEET 1 OF 1
--------------	------------	--------------