





APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

| Rev | AWO # | Description    | Date     | Appr  |
|-----|-------|----------------|----------|-------|
| -   |       | RELEASED       | 5/5/14   |       |
| A   |       | REVISED SPEC.  | 6/4/14   | HR/VY |
| B   |       | UPDATE DRAWING | 1/9/18   | AY/KC |
| C   |       | UPDATE DRAWING | 10/20/20 | LH/EY |



RECOMMENDED PCB LAYOUT



#### SPECIFICATIONS:

##### Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Contact: Copper Alloy, Tin plated

##### Electrical:

Voltage rating: 300 VAC

Current rating: 8 Amp

Dielectric withstanding voltage: 1,600 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 24

A= .150 [3.81] x No. of Spaces + .181 [4.60]

B= .150 [3.81] x No. of Spaces

UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED

| INCHES |        | HOLES |       |
|--------|--------|-------|-------|
| .X     | ± .10  | Ø.X   | ±.10  |
| .XX    | ± .020 | Ø.XX  | ±.015 |
| .XXX   | ± .015 | Ø.XXX | ±.010 |

| APPROVALS |    | DATE   |
|-----------|----|--------|
| DRAWN     | HR | 5/5/14 |
| CHECKED   | SY | 5/5/14 |
| APPROVED  |    |        |

**ADAM**  
**TECH**

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE

TERMINAL BLOCK, STRAIGHT, .150" [3.81] PITCH

SIZE

X

PART NO.

EBRA-XX-B

REV.

C

REF: S00067C

SCALE: NTS

SHEET 1 OF 1