





Rev	AWO #	Description	Date	Appr
-		RELEASED	1/6/05	

APPROVED: _____

DATE: _____ TITLE: _____



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 1 Amp max.

Contact resistance: 20 mohms max. initial

Insulation resistance: 5,000 Mohms min.

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 01 thru 32
A = .050 [1.27] x No. of Positions Per Row
B = .050 [1.27] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
INCHES			TITLE		
.X ± .10			.050 [1.27] SINGLE ROW PIN HEADER		
.XX ± .020			PART NO.		
.XXX ± .015			HPH1-A-XX-UA		
.XXX ± .010			REV.		
APPROVALS			DATE		
DRAWN			SS		
CHECKED			1/6/05		
APPROVED			X		
REF:			SCALE: NTS		
			SHEET 1 OF 1		