




Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/05	

APPROVED: _____

DATE: _____ TITLE: _____



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
INCHES			TITLE .100 [2.54] LOCKING HEADER REVERSE RIGHT ANGLE, PCB		
HOLES			PART NO. LHA-XX-TRB		
.X ± .10			SIZE		
.XX ± .020			X		
.XXX ± .015			REV.		
.XXX ± .010			DATE		
APPROVALS			4/8/05		
DRAWN			SS		
CHECKED					
APPROVED					
REF:			SCALE: NTS		
			SHEET 1 OF 1		