







APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/13/18	



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: Stainless Steel

Plating:

Gold flash over Nickel underplate on contact area

Electrical:

Current rating: 1 A max

Contact resistance: 30 mohms max.

Insulation resistance: 100 Mohms min.

Dielectric withstanding voltage: 100 VAC for 1 minute

Temperature Rating:

Temperature range: -30°C to +80°C

Environmental:

Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES .X ± .10 .XX ± .020 .XXX ± .015		Ø.X ± .10 Ø.XX ± .015 Ø.XXX ± .010	
APPROVALS		DATE	
DRAWN	HR	3/13/18	
CHECKED	RC1	3/13/18	
APPROVED			

ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
TITLE		MICRO USB, TYPE B, SINGLE PORT, SOCKET, RIGHT ANGLE, SMT TYPE	
SIZE X	PART NO. MCR-B-S-RA-SMT-CS14-T/R	REV -	
REF: S00097C	SCALE: NTS	SHEET 1 OF 1	