


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/9/17	
A		UPDATE SPEC.	10/17/17	AY/TY



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Stainless Steel, Matte tin plated

Plating:

10u" Gold over Nickel underplate overall

Electrical:

Rated current: PIN 1 & 5 => 1.8A

PIN 2, 3 & 4 => 0.5A.

Rated Voltage: 30 VAC

Environmental:

Lead free, RoHS compliant.



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS DRAWN AY 1/9/17 CHECKED MY 1/9/17 APPROVED		TITLE MICRO USB B TYPE, FEMALE, VERTICAL SMT, W/PEG SIZE X PART NO. MCR-B-S-V-SMT-P-CS1-10-PP-T/R REV. A REF: S00126T SCALE: NTS SHEET 1 OF 1	