





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	11960	RELEASED	3/9/15	
A		UPDATED DRAWING	4/2/15	HR/LL



SPECIFICATIONS:

Material: HI-Temp Thermoplastic, rated UL94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Shell: SUS301, Nickel plated
Latch: SUS301
Plating: Gold over Nickel underplate on contact area, Tin over Copper underplate on tails
Electrical:
Current rating: Signal: 1 A min.
Power: 1.8 A for all Contact
0.5 A min. for contact 2, 3, 4
Contact resistance: 30 mohms max.
Temperature Rating: Operating temperature: -30°C to +80°C
Environmental:
Lead free, RoHS compliant.

RoHS
COMPLIANT

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MICRO USB B TYPE PLUG, 5P

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
.X	± .10	ØX	± .10	MICRO USB B TYPE PLUG, 5P			
.XX	± .020	ØXX	± .015				
.XXX	± .015	ØXXX	± .010				
APPROVALS							
DRAWN	AY	3/9/15	DATE	SIZE	PART NO.	REV.	
CHECKED	TW	3/9/15		X	MCR-B-MPLUG-06	A	
APPROVED				REF:	S00097C	SCALE: NTS	SHEET 1 OF 1