





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/8/22	
A		UPDATE SPEC.	11/8/22	LH/RC



SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Housing: PA, rated UL 94V-0

Center Contacts: Brass

Outer Contacts (Interface): SUS304, Matte Tin plated

Shell: Zamak, Tin Plated

Contact Plating:

Contact area: 6u" Gold Plated

Solder tails area: 80-160u" Matte Tin Plated

Underplate: 80-160u" Nickel underplate overall

Electrical:

Working voltage: ≤ 60 VDC

Power Current : ≤ 1A DC

Impedance: 50Ω

Frequency: DC to 9 GHz

Center Contact Resistance: ≤15m Ω

Outer Contact Resistance: ≤5m Ω

Insulation resistance: ≥1x10³ MΩ

Dielectric withstanding voltage: 800 Vrms

Mechanical:

Mating Cycles: ≥ 25 Cycles

Engagement force: ≤ 15N

Disengagement force: ≥ 2N

Retention Force Latch: ≥ 110N

Coding Efficiency: ≥ 150N

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

	MM	ANGLE
X	± 0.50	± 5°
.X	± 0.30	
.XX	± 0.20	

DRAWN	LH	6/8/22
CHECKED	JL	6/8/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

**ADAM
TECH**

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE		MINI FAKRA RIGHT ANGLE PLUG		
SIZE	PART NO.	MHSD-01X-AM-PRX-T/R		REV. A
REF: S00013T	SCALE: NTS	SHEET 1 OF 3		

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev





AWO #

Description

Date

Appr

SEE SHT 1 OF 3 FOR REVISION

PartNumber	MHSD-01X-AM-PRA-T/R	MHSD-01X-AM-PRC-T/R
Direction	STANDARD ORIENTATION	90° ORIENTATION
		
PartNumber	MHSD-01X-AM-PRB-T/R	MHSD-01X-AM-PRD-T/R
Direction	180° ORIENTATION	270° ORIENTATION
		

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

	MM	ANGLE
.X	± 0.50	± 5°
.X	± 0.30	
.XX	± 0.20	

DRAWN LH 6/8/22

CHECKED JL 6/8/22

APPROVED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH**ADAM
TECH**909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

MINI FAKRA RIGHT ANGLE PLUG

SIZE
X

PART NO.

MHSD-01X-AM-PRX-T/R

REV.
A

REF: S00013T

SCALE: NTS

SHEET 2 OF 3

6

5

4

3

2

1

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description









Date

Appr

SEE SHT 1 OF 3 FOR REVISION

Currently only A, B, Z styles Other styles need to open the mold

MHSD-01X-AM-PRX-T/R

Coding	A	B	C	D	E	F	G
Plug							
Color	BLACK	WHITE	BLUE	CLARET VIOLET	GREEN	BROWN	GREY
Coding	H	J	K	N	Z		
Plug							
Color	LIGHT PINK	BEIGE	CURRY	PASTEL GREEN	WATER BLUE		

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

	MM	ANGLE
X.	± 0.50	± 5°
.X	± 0.30	
.XX	± 0.20	

DRAWN	LH	6/8/22
CHECKED	JL	6/8/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH**ADAM**
TECH909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

MINI FAKRA RIGHT ANGLE PLUG

SIZE
X

PART NO.

MHSD-01X-AM-PRX-T/R

REV.
A

REF: S00013T

SCALE: NTS

SHEET 3 OF 3

6

5

4

3

2

1