





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/16/09	
A		UPDATE DRAWING	8/15/18	AY/TY



SPECIFICATIONS:

Material:

Insulator: ABS, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Wire: 26 Awg, UL 1061

Plating:

Gold over Nickel underplate on mating area

Electrical:

Voltage rating: 125 VAC max

Current rating: 1.5 Amp

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1,000 VAC or 1,500 VDC for 1 minute

Temperature Rating:

Operating temperature: 0°C to +70°C

Environmental:

Lead free, RoHS compliant.



X	PLATING
0	15 μ in Gold
1	30 μ in Gold
2	50 μ in Gold

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	DY	6/16/09
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
WIRE LEADED TELEPHONE JACK, 616E,
4P4C, 26AWG, STRIPPED, COLOR BLACK

SIZE X	PART NO. MTJP-616E-X-A1-1	REV. A
REF: S00005C	SCALE: NTS	SHEET 1 OF 1