







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	04/20/05	
A		REVISED & REDRAWN	10/09/06	
B		UPDATED DRAWING	1/25/16	AY/MW



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Brass, nickel plated

Plating:

Gold flash over Nickel underplate on contact area,

Tin over Copper underplate on PCB tails

Electrical:

Operating voltage: 30 VAC max

Current rating: 1 Amps max

Contact resistance: 50 Mohms max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 100 VAC for 1 minute

Temperature Rating:

Operating temperature: -20°C to +60°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	04/20/05
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
MINI USB, TYPE B, 5PIN, RIGHT ANGLE,
PCB MOUNT

SIZE	PART NO.	REV.
X	MUSB-B5-S-RA	B
REF:	S00005C	SCALE: NTS
SHEET 1 OF 1		