



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/4/15	



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: Brass, Nickel plated

Plating:

Gold Flash over Nickel underplate on contact area,

Tin over Copper underplate on SMT tails

Electrical:

Voltage rating: 30 VDC max.

Current rating: 1.0 Amp max.

Contact resistance: 50 mohms max.

Insulation resistance: 100 Mohms min.

Dielectric withstanding voltage: 300 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ±.010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE		
DATE			MINI USB, TYPE B, 5 PIN, SINGLE PORT		
DRAWN HR 3/4/15			RIGHT ANGLE, SMT		
CHECKED NP 3/4/15			SIZE PART NO.		REV.
APPROVED			X MUSB-B5-S-RA-TSMT-CS1		-
			REF: S00126T SCALE: NTS		SHEET 1 OF 1