




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/06/10	
A		UPDATE SHAPE	11/19/14	AV/RL



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

- Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Copper Alloy
Shell: SPCC, Nickel plated
Plating:
Gold Flash over Nickel underplate on contact area,
Tin over Copper underplate on SMT tails
Electrical:
Operating voltage: 30 VAC max.
Current rating: 1 Amp max.
Contact resistance: 50 mohms max.
Insulation resistance: 100 Mohms min.
Dielectric withstanding voltage: 300 VAC for 1 minute
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: MINI USB, TYPE B, 5 PIN, SINGLE PORT
RIGHT ANGLE, SMT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES X ± .10 ØX ± .10 XX ± .020 ØXX ± .015 .XXX ± .015 ØXXX ± .010												ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710											
APPROVALS						DATE						TITLE											
DRAWN						DY						4/06/10						MINI USB, TYPE B, 5 PIN, SINGLE PORT RIGHT ANGLE, SMT					
CHECKED												SIZE						PART NO.					
APPROVED												X						MUSB-B5-S-RA-TSMT-NP					
REF: S00126T						SCALE: NTS						SHEET 1 OF 1						REV. A					