

6

5

4

3





2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/25/07	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold Flash over Nickel underplate on contact area

Tin over Copper underplate on PCB tails

Electrical:

Operating voltage: 30 VAC max

Current rating: 1 Amps max

Contact resistance: 50 Mohms max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 100 VAC for 1 minute

Temperature Rating:

Operating temperature: -20°C to +60°C

Environmental:

Lead free, RoHS compliant.



A

B

C

D

A

B

C

D

ADAM TECH

909 Ratway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

MINI USB, TYPE B, 5PIN, VERTICAL

PCB MOUNT

MUSB-B5-S-VT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM TOLERANCES: EXCEPT AS NOTED				TITLE			
XX ± 0.25 XXX ± 0.20				MINI USB, TYPE B, 5PIN, VERTICAL PCB MOUNT			
APPROVALS				SIZE PART NO.			
DRAWN SS				9/25/07			
CHECKED				X			
APPROVED				REF: SCALE: NTS SHEET 1 OF 1			

6

5

4

3

2

1