





Rev	AWO #	Description	Date	Appr
-		RELEASED	6/2/05	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Natural

Contacts: Phosphor Bronze

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max.

Current rating: 3 Amps max.

Contact resistance: 10 mohms max. initial

Insulation resistance: 1,000 Mohms min.

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Mechanical:

Recommended PCB thickness: 0.063" (1.60mm)

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 02 thru 20
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.100 [2.54] PCB CONNECTOR

BOARD HOOKS, BOTTOM ENTRY

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				Holes			
				.X				.XX			
				.XXX				.XXX			
APPROVALS				DATE				DATE			
DRAWN	SS	6/2/05		SIZE	PART NO.	PCE-C-XX	REV.	SIZE	PART NO.	PCE-C-XX	REV.
CHECKED				X				X			
APPROVED				REF:	SCALE: NTS	SHEET 1 OF 1		REF:	SCALE: NTS	SHEET 1 OF 1	