



Rev	AWO #	Description	Date	Appr
-		RELEASED	10/5/04	

6 5 4 3 2 1

APPROVED: _____

DATE: _____ TITLE: _____

PCB LAYOUT



A = .100 [2.54] X No. of Positions.
B = .100 [2.54] X No. of Spaces.
1 THRU 40 PINS AVAILABLE

SPECIFICATIONS:

Material:
Insulator: PBT, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating:
Tin over Copper underplate overall
Electrical:
Operating voltage: 250 VAC max
Current rating: 3 Amps max
Insulation resistance: 5000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -55°C to +105°C
Environment:
Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

PIN HEADER, SINGLE ROW, .100 PITCH
STRAIGHT, .235 MATING / .120 TAIL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
.X	± .10	ØX	± .10	PIN HEADER, SINGLE ROW, .100 PITCH			
.XX	± .020	ØXX	± .015	STRAIGHT, .235 MATING / .120 TAIL			
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN	SS	10/5/04					
CHECKED							
APPROVED							