

6

5

4

3



2

1



Rev	AWO #	Description	Date	Appr
-		RELEASED	10/10/07	

APPROVED: _____

DATE: _____ TITLE: _____



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold Flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 5,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 1 thru 40
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Positions - 1

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

.100 [2.54] SINGLE ROW PIN HEADER
RIGHT ANGLE, HIGH PROFILE, GOLD PLATED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		TITLE	
INCHES	HOLES	RIGHT ANGLE, HIGH PROFILE, GOLD PLATED	
.X ± .10	Ø.X ± .10	SIZE PART NO.	
.XX ± .020	Ø.XX ± .015	X	PH1RA-XX-UA
.XXX ± .015	Ø.XXX ± .010	REV.	
APPROVALS	DATE	REF:	
DRAWN	SS	SCALE: NTS	
CHECKED		SHEET 1 OF 1	
APPROVED			