





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/4/05	
A		REVISED SPEC.	03/26/13	



SPECIFICATIONS:
Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating:
Gold flash over Nickel underplate overall

Electrical:
Current rating: 3 Amps max
Contact resistance: 20 mohms max
Insulation resistance: 5,000 Mohms min @ 500 VDC
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:
Lead free, RoHS compliant

Positions: 1 thru 40
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES	HOLES	DATE	TITLE	SIZE	PART NO.	REV.	
.X ± .10	ØX ± .10		.100 [2.54] SINGLE ROW PIN HEADER	X	PH1RB-XX-UA	A	
.XX ± .020	ØXX ± .015		RIGHT ANGLE, LOW PROFILE, GOLD PLATED				
.XXX ± .015	ØXXX ± .010						
DRAWN	SS	4/4/05					
CHECKED							
APPROVED							
REF:	S00039T	SCALE: NTS	SHEET 1 OF 1				