







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/7/22	
A		UPDATED TITLE	7/14/23	JJ/RC
B		ADDED SPEC.	7/25/23	LH/RC



RECOMMENDED PANEL CUT



SPECIFICATIONS:

Electrical:

Voltage rating: 115/250 VAC

Current rating: 115/250 VAC: 3A RMS max

Leakage Current: Each Line To Ground

@115VAC/60HZ 2.0uA max

@250VAC/50HZ 5.0uA max

Hipot Rating(For 1 Minute)

A. Line to Ground: 2,250 VDC

B. Line to Line: 500 VDC

IR: 50 Mohm @500 VDC Any Input or Output to Ground

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



Medical Grade



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X $\pm$.10	ϕ .X $\pm$.10
.XX $\pm$.020	ϕ .XX $\pm$.015
.XXX $\pm$.015	ϕ .XXX $\pm$.010

DRAWN	WX	11/7/22
CHECKED	RC	11/7/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
FILTERED POWR ENTRY MODULE, MEDICAL GRADE
115/250VAC 3A, DUAL FUSE INLET, FLANGE MOUNT

SIZE X	PART NO. PLF-11B2-3A-Q-R5	REV. A
REF: S00205C	SCALE: NTS	SHEET 1 OF 2


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 2 FOR REVISION				

INSERTION LOSS(IN 50 ohm system according IEC/CISPR

_____ (common mode)
_____ (differential mode)



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010



909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

DRAWN	WX	11/7/22
CHECKED	RC	11/7/22
APPROVED		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH		

TITLE FILTERED POWR ENTRY MODULE, MEDICAL GRADE 115/250VAC 3A, DUAL FUSE INLET, FLANGE MOUNT		
SIZE X	PART NO. PLF-11B2-3A-Q-R5	REV. B
REF: S00205C	SCALE: NTS	SHEET 2 OF 2