







APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/27/16	
A		UPDATE DRAWING	8/16/22	LH/NL



RECOMMENDED CABLE STRIPPING DIMS



RECOMMENDED MOUNTING HOLE

SPACER	PTFE	WHITE
HEX NUT	BRASS	GOLD
WASHER	S50C	GOLD
FERRULE	BRASS	GOLD
SLEEVE	BRASS	GOLD
CONTACT PIN	BRASS	GOLD
INSULATOR	PTFE	WHITE
BURREL	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Frequency range: DC-6 GHz

Nominal Impedance: 50 Ohms

Working Voltage: 170 VOLTS max

Proof Voltage: 500 VOLTS

VSWR : 1.3 Max @ 3 GHz

Temperature Rating:

Operating temperature: -65°C to +165°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

DRAWN	AY	5/27/16
CHECKED	SY	5/27/16
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE SMA JACK STR BULKHEAD, 50OHM, 178U		
SIZE X	PART NO. RF2-06A-T-21-50-G	REV. A
REF: S00277T	SCALE: NTS	SHEET 1 OF 1